

## 8502SGO1V06

NEMA Contactor, Type S, nonreversing, Size 5, 270A, 1 phase, up to 100 kA, 2 pole, 480 VAC coil, open



### Main

Product Type	Contactors
Product Range	8502S
Contactors Type	Non-reversing

### Complementary

NEMA Size	5
Rated Current	270 A
Number of Poles	2P
Maximum Voltage Rating	600 V AC
Phase	1 phase
Horsepower Rating	Not rated
SCCR	Circuit-breaker 400 A maximum, SCCR: 100 kA at 480 V AC Fuse J 400 A maximum, SCCR: 100 kA at 600 V AC Fuse T 400 A maximum, SCCR: 100 kA at 600 V AC Fuse RK1 400 A maximum, SCCR: 100 kA at 600 V AC Fuse RK5 400 A maximum, SCCR: 100 kA at 600 V AC
Coil Voltage	480 V AC 60 Hz 440 V AC 50 Hz
Control Circuit Type	Common control circuit
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Other Equipment	Fuse not supplied
Terminal Type	Screw clamp terminals
Height	12.31 in (312.67 mm)
Width	8.67 in (220.22 mm)
Depth	8.75 in (222.25 mm)

### Environmental

Enclosure Type	Not rated (open device)
Certifications	UL listed file E78351 CCN NLDX[RETURN]CSA

### Ordering and shipping details

Category	21194-8502,36SG(NOT S*R,S*T,S*W)
Discount Schedule	CP1
GTIN	00785901862062
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Not compliant
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------