

Product data sheet

Characteristics

8502WFO3V02

Vacuum Contactor, 8502V, nonreversing, Size 4, 135A, 100 HP at 575 VAC, 3 phase, 3 pole, 120 VAC coil, open



Main

Product Type	Vacuum contactor
Product Range	8502W
Contactors Type	Non-reversing

Complementary

NEMA Size	4
Rated Current	135 A
Number of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Horsepower Rating	40 HP 200 V AC 50 HP 230 V AC 100 HP 460 V AC 100 HP 575 V AC
Coil Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Control Circuit Type	Common control circuit
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Other Equipment	Fuse not supplied
Height	66.14 in (168 cm)
Width	4.65 in (118 mm)
Depth	59.45 in (151 cm)

Environmental

Enclosure Type	No enclosure rating (open device)
Certifications	UL Listed[RETURN]CSA


Ordering and shipping details

Category	US10CP121208
Discount Schedule	0CP1
GTIN	00785901138198
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.50 in (21.59 cm)
Package 1 Width	7.80 in (19.812 cm)
Package 1 Length	8.50 in (21.59 cm)
Package 1 Weight	9.90 lb(US) (4.491 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Under investigation
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------