

Product data sheet

Characteristics

8502WGO3V02

Vacuum Contactor, 8502V, nonreversing, Size 5, 270A, 200HP at 575VAC, 3 phase, 3 pole, 120VAC coil, open



Main

Product Type	Vacuum contactor
Product Range	8502W
Contactors Type	Non-reversing

Complementary

NEMA Size	5
Rated Current	270 A
Number of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Horsepower Rating	75 HP 200 V AC 100 HP 230 V AC 200 HP 460 V AC 200 HP 575 V AC
Coil Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Control Circuit Type	Common control circuit
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Other Equipment	Fuse not supplied
Terminal Type	Screw connector
Height	12.52 in (318 mm)
Width	79.13 in (201 cm)
Depth	61.42 in (156 cm)

Environmental

Enclosure Type	Not rated (open device)
Certifications	UL Listed[RETURN]CSA


Ordering and shipping details

Category	US10CP121208
Discount Schedule	OCP1
GTIN	785901138174
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.52 in (31.8 cm)
Package 1 Width	79.13 in (201.0 cm)
Package 1 Length	61.42 in (156.0 cm)
Package 1 Weight	27.07 lb(US) (12.279 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Under investigation
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------