

Product data sheet

Characteristics

8536SEG1V08

NEMA Motor Starter, Type S, nonreversing, Size 3, 90A, 50 HP at 460 VAC, 5 kA SCCR, 3 phase, 3 pole, melting alloy, 208 VAC coil, NEMA 1

Main

Product Type	Motor starter
Product Range	S
Starter Type	Non reversing

Complementary

NEMA Size	3
Rated Current	90 A
Number of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type of Overload	Melting alloy 3
Horsepower Rating	25 HP 200 V AC 30 HP 230 V AC 50 HP 460 V AC 50 HP 575 V AC
SCCR	Circuit-breaker: 5 kA at 600 V AC Fuse: 5 kA at 600 V AC
Coil Voltage	208 V AC 60 Hz
Control Circuit Type	Common control circuit
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Terminal Type	Screw clamp terminals
Height	21.81 in (553.97 mm)
Width	11.44 in (290.58 mm)
Depth	8.38 in (212.85 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel
Certifications	UL Listed[RETURN]CSA[RETURN]NEMA

Ordering and shipping details

Category	US10CP121193
Discount Schedule	OCP1
GTIN	785901788225
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.20 in (23.368 cm)
Package 1 Width	12.00 in (30.48 cm)
Package 1 Length	22.40 in (56.896 cm)
Package 1 Weight	35.080 lb(US) (15.912 kg)

Offer Sustainability

Packaging without single use plastic	Yes
Packaging made with recycled cardboard	No
California proposition 65	"WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov "
REACH Regulation	REACH Declaration
EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS Declaration
Take-back	No

Contractual warranty

Warranty	18 months
----------	-----------