

Product data sheet

Characteristics

8538SBG11V02S

NEMA combination starter, Type S, nonfusible disconnect, Size 0, 18A, 5HP at 600VAC, 3 phase, 3 pole, 120VAC coil, NEMA 1



Main

Product	Combination Starter
Type	S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	3 Hp 200 V AC, 3 phase 3 Hp 230 V AC, 3 phase 5 Hp 460 V AC, 3 phase 5 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Thermal overload type	Melting alloy 3
Disconnect Type	Non-fusible disconnect switch
NEMA size	0

Environment

Enclosure Type	NEMA 1 painted sheet steel with external reset
----------------	--

Ordering and shipping details

Category	US10CP121212
Discount Schedule	0CP1
GTIN	785901744542
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.70 in (27.178 cm)
Package 1 Width	13.10 in (33.274 cm)
Package 1 Length	29.00 in (73.66 cm)
Package 1 Weight	34.20 lb(US) (15.513 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------