

## Product data sheet

### Characteristics

# 8538SBG33V02S

NEMA combination starter, Type S, 30A fusible disconnect, Size 0, 18A, 5HP at 600VAC, 3 phase, 3 pole, melting alloy, 120VAC coil, NEMA 1



### Main

Product	Combination Starter
Type	S
Control Circuit Type	Separate control circuit

### Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Starter Type	Non reversing
Line Rated Current	18 A
Number of Poles	3P
Horsepower Rating	5 Hp 460 V AC, 3 phase 5 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Thermal overload type	Melting alloy 3
Disconnect Type	Fusible disconnect switch R, 30 A
NEMA size	0
Height	22.50 in (571.50 mm)
Depth	8.34 in (211.84 mm)
Width	9.50 in (241.30 mm)

### Environment

Enclosure Type	NEMA 1 painted sheet steel with external reset
Product Certifications	UL Listed[RETURN]CSA



### Ordering and shipping details

Category	US10CP121212
Discount Schedule	OCP1
GTIN	785901020745
Returnability	No
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.70 in (27.178 cm)
Package 1 Width	10.50 in (26.67 cm)
Package 1 Length	26.00 in (66.04 cm)
Package 1 Weight	45.00 lb(US) (20.412 kg)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Not compliant
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------