

8538SCA44V02S

NEMA combination starter, Type S, 30A fusible disconnect, Size 1, 27A, 10HP at 600VAC, 3 phase, 3 pole, 120VAC coil, NEMA 12



Main

Product	Combination Starter
Type	S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Starter Type	Non reversing
Line Rated Current	27 A
Number of Poles	3P
Horsepower Rating	10 Hp 460 V AC, 3 phase 10 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Thermal overload type	Melting alloy 3
Disconnect Type	Fusible disconnect switch R, 30 A
NEMA size	1
Height	24.0 in (609.60 mm)
Depth	9.5 in (241.30 mm)
Width	8.34 in (211.84 mm)

Environment

Enclosure Type	NEMA 12 painted sheet steel with external reset
Product Certifications	UL[RETURN]CSA



Ordering and shipping details

Category	US10CP121213
Discount Schedule	OCP1
GTIN	785901021063
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.00 in (27.94 cm)
Package 1 Width	13.10 in (33.274 cm)
Package 1 Length	29.00 in (73.66 cm)
Package 1 Weight	32.85 lb(US) (14.901 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Not compliant
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------