

# Product data sheet

## Characteristics

# 8538SCG12V02S

NEMA combination starter, Type S, 30A fusible disconnect, Size 1, 27A, 5HP at 240VAC, 3 phase, 3 pole, 120VAC coil, NEMA 1



## Main

Product	Combination Starter
Type	S
Control Circuit Type	Separate control circuit

## Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	5 Hp 200 V AC, 3 phase 5 hp 230 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Thermal overload type	Melting alloy 3
Disconnect Type	Fusible disconnect switch H, 30 A
NEMA size	1

## Environment

Enclosure Type	NEMA 1 painted sheet steel with external reset
----------------	--

## Ordering and shipping details

Category	US10CP121213
Discount Schedule	0CP1
GTIN	785901748298
Returnability	No
Country of origin	US

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.00 in (27.94 cm)
Package 1 Width	13.10 in (33.274 cm)
Package 1 Length	29.00 in (73.66 cm)
Package 1 Weight	35.20 lb(US) (15.967 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Not compliant
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

Contractual warranty

Warranty	18 months
----------	-----------