

Product data sheet

Characteristics

8702SCO2V03

NEMA Contactor, Type S, reversing, horizontal, Size 1, 27A, 3 HP at 230 VAC, single phase, 2 pole, 240 VAC coil, open style



Main

Product Type	Contactors
Product Range	Type S
Contactors Type	Reversing

Complementary

NEMA Size	1
Rated Current	27 A
Number of Poles	2P
Mounting Orientation	Horizontal
Wiring Mode	3 wires
Maximum Voltage Rating	600 V AC
Phase	1 phase
Horsepower Rating	3 HP 230 V AC 2 HP 115 V AC
Coil Voltage	220 V AC 50 Hz 240 V AC 60 Hz
Control Circuit Type	Common control circuit
Control Units	No control units
Other Equipment	Fuse not supplied
Terminal Type	Screw clamp terminals
Height	5.00 in (127 mm)
Width	7.13 in (181 mm)
Depth	5.31 in (135 mm)

Environment

Enclosure Type	Not rated (open device)
Certifications	CSA[RETURN]UL Listed


Ordering and shipping details

Category	US10CP121272
Discount Schedule	0CP1
GTIN	785901125457
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.00 in (15.24 cm)
Package 1 Width	4.50 in (11.43 cm)
Package 1 Length	8.00 in (20.32 cm)
Package 1 Weight	7.14 lb(US) (3.238 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Not compliant
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------