


8736SBO10V02S

NEMA starter, Type S, reversing, vertical, Size 0, 18A, 5HP at 575VAC, 5kA SSCR, 3 phase, 3 pole, melting alloy overload, 120VAC coil, open



Main

Product Type	Starter
Product Range	S
Starter Type	Reversing

Complementary

NEMA Size	0
Rated Current	18 A
Number of Poles	3P
Mounting Orientation	Vertical
Wiring Mode	3 wires
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type of Overload	Melting alloy 3
Horsepower Rating	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
SCCR	Circuit-breaker: 5 kA at 600 V AC Fuse: 5 kA at 600 V AC
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Control Circuit Type	Separate control circuit
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Terminal Type	Screw clamp terminals
Height	11.52 in (292.61 mm)
Width	5.47 in (138.94 mm)
Depth	5.31 in (134.87 mm)

Environment

Enclosure Type	Not rated (open device)
Certifications	UL Listed[RETURN]CSA


Ordering and shipping details

Category	US10CP121271
Discount Schedule	OCP1
GTIN	785901102410
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.60 in (21.844 cm)
Package 1 Width	11.30 in (28.702 cm)
Package 1 Length	13.80 in (35.052 cm)
Package 1 Weight	10.45 lb(US) (4.74 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Not compliant
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------