


## 8736SCO7V02S

NEMA starter, Type S, reversing, vertical, Size 1, 27A, 10HP at 575VAC, 5kA SCCR, 3 phase, 3 pole, melting alloy overload, 120VAC coil, open



### Main

Product Type	Starter
Product Range	S
Starter Type	Reversing

### Complementary

NEMA Size	1
Rated Current	27 A
Number of Poles	3P
Mounting Orientation	Vertical
Wiring Mode	3 wires
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type of Overload	Melting alloy 3
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
SCCR	Circuit-breaker: 5 kA at 600 V AC Fuse: 5 kA at 600 V AC
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Control Circuit Type	Separate control circuit
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Terminal Type	Screw clamp terminals
Height	11.52 in (292.61 mm)
Width	5.47 in (138.94 mm)
Depth	5.31 in (134.87 mm)

### Environment

Enclosure Type	Not rated (open device)
Certifications	UL Listed[RETURN]CSA


## Ordering and shipping details

Category	US10CP121272
Discount Schedule	0CP1
GTIN	785901874409
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.50 in (21.6 cm)
Package 1 Width	11.30 in (28.7 cm)
Package 1 Length	13.70 in (34.8 cm)
Package 1 Weight	10.41 lb(US) (4.72 kg)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Not compliant
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------