

Main

Product or Component Type	Starter
Range of Product	Type S

Complementary

Control circuit	Separate control circuit
Control type	Without
NEMA degree of protection	Not rated (open device)
Auxiliary contact composition	Without
Maximum Horse Power Rating	5 Hp 200 V AC, 3 phase 5 Hp 230 V AC, 3 phase 7.5 hp 460/575 V AC, 3 phase
Poles description	3P
Maximum operating voltage	600 V AC
NEMA size	1
[Uc] control circuit voltage	120 V AC 60 Hz 110 V AC 50 Hz
Local signalling	Without pilot light
Motor starter type	2 speed
Electrical Connection	Lugs
Thermal overload type	Melting alloy
Number of thermal units required	6
Asynchronous motor control profile	Constant horsepower
Maximum operating current	27 A

Environment

Product Certifications	UL listed file E78351 CCN NLDX[RETURN]CSA LR60905 class 3211 04
------------------------	---


Ordering and shipping details

Category	US10CP121302
Discount Schedule	OCP1
GTIN	785901497226
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.50 in (21.59 cm)
Package 1 Width	8.00 in (20.32 cm)
Package 1 Length	12.50 in (31.75 cm)
Package 1 Weight	6.79 lb(US) (3.079 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Not compliant
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------