



Main

Product or Component Type	Electrically Held Lighting Contactor
Range of Product	8903L
Control Circuit	Separate control circuit

Complementary

Control Circuit Voltage	277 V AC 60 Hz
Inrush power in VA	150 VA 60 Hz
Hold-in power consumption in VA	30 VA 60 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number of Poles	4P 4 NO
Control Unit	No control units
Pilot Light	No indicator
Electrical Connection	Screw-clamp terminals
Height	12.68 in (322 mm)
Depth	6.02 in (153 mm)
Width	7.80 in (198 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel surface
Product Certifications	UL Listed[RETURN]CSA

Ordering and shipping details

Category	US10CP121321
Discount Schedule	OCP1
GTIN	785901625650
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.40 in (18.8 cm)
Package 1 Width	8.31 in (21.1 cm)
Package 1 Length	13.70 in (34.8 cm)
Package 1 Weight	9.63 lb(US) (4.37 kg)

Unit Type of Package 2	PAL
Number of Units in Package 2	50
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	482.43 lb(US) (218.828 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------