



## Main

Product or Component Type	Electrically Held Lighting Contactor
Range of Product	8903L
Control Circuit	Separate control circuit

## Complementary

Control Circuit Voltage	277 V AC 60 Hz
Inrush power in VA	150 VA 60 Hz
Hold-in power consumption in VA	30 VA 60 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number of Poles	6P 6 NO
Control Unit	No control units
Pilot Light	No indicator
Electrical Connection	Screw-clamp terminals
Height	12.68 in (322 mm)
Depth	6.02 in (153 mm)
Width	7.80 in (198 mm)

## Environment

Enclosure Type	NEMA 1 painted sheet steel surface
Product Certifications	UL Listed[RETURN]CSA

## Ordering and shipping details

Category	US10CP121321
Discount Schedule	OCP1
GTIN	785901102366
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.52 in (19.1 cm)
Package 1 Width	8.39 in (21.3 cm)
Package 1 Length	13.70 in (34.8 cm)
Package 1 Weight	10.01 lb(US) (4.54 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

## Contractual warranty

Warranty	18 months
----------	-----------