



### Main

|                           |                                      |
|---------------------------|--------------------------------------|
| Product or Component Type | Mechanically Held Lighting Contactor |
| Range of Product          | 8903LX                               |
| Control Circuit           | Separate control circuit             |

### Complementary

|                       |                                   |
|-----------------------|-----------------------------------|
| Control Voltage       | 277 V AC 60 Hz                    |
| Inrush power in VA    | 180 VA 60 Hz<br>25 VA 50/60 Hz    |
| Current Rating        | 20 A tungsten<br>30 A fluorescent |
| Number of Poles       | 8P 8 NO                           |
| Control Unit          | No control units                  |
| Pilot Light           | No indicator                      |
| Other Options         | None                              |
| Electrical Connection | Screw-clamp terminals             |
| Height                | 12.68 in (322 mm)                 |
| Depth                 | 6.02 in (153 mm)                  |
| Width                 | 7.80 in (198 mm)                  |

### Environment

|                        |                                    |
|------------------------|------------------------------------|
| Enclosure Type         | NEMA 1 painted sheet steel surface |
| Product Certifications | UL Listed[RETURN]CSA               |

### Ordering and shipping details

|                   |              |
|-------------------|--------------|
| Category          | US10CP121322 |
| Discount Schedule | OCP1         |
| GTIN              | 785901057413 |
| Returnability     | No           |
| Country of origin | MX           |

### Packing Units

|                              |                         |
|------------------------------|-------------------------|
| Unit Type of Package 1       | PCE                     |
| Number of Units in Package 1 | 1                       |
| Package 1 Height             | 7.60 in (19.304 cm)     |
| Package 1 Width              | 8.10 in (20.574 cm)     |
| Package 1 Length             | 12.80 in (32.512 cm)    |
| Package 1 Weight             | 11.72 lb(US) (5.316 kg) |

## Offer Sustainability

|                             |                                                                                                            |
|-----------------------------|------------------------------------------------------------------------------------------------------------|
| Sustainable offer status    | Green Premium product                                                                                      |
| California proposition 65   | WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation            | <a href="#">REACH Declaration</a>                                                                          |
| REACH free of SVHC          | Yes                                                                                                        |
| EU RoHS Directive           | Compliant <a href="#">EU RoHS Declaration</a>                                                              |
| Toxic heavy metal free      | Yes                                                                                                        |
| Mercury free                | Yes                                                                                                        |
| China RoHS Regulation       | <a href="#">China RoHS Declaration</a>                                                                     |
| RoHS exemption information  | <a href="#">Yes</a>                                                                                        |
| Environmental Disclosure    | <a href="#">Product Environmental Profile</a>                                                              |
| Circularity Profile         | No need of specific recycling operations                                                                   |
| PVC free                    | Yes                                                                                                        |
| Halogen content performance | Halogen free plastic parts product                                                                         |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|