

Product data sheet

Characteristics

8903SMG1V02

Contacteur, Type S, multipole lighting,
electrically held, 30A, 2 pole, 110/120VAC
50/60Hz coil, NEMA 1



Main

| | |
|---------|--------------------------------------|
| Product | Electrically Held Lighting Contactor |
| Type | S |

Complementary

| | |
|-------------------------|----------------------------------|
| Control Circuit Voltage | 120 V AC 60 Hz 110 V AC 50 Hz |
| Current Rating | 30 A |
| Number of Poles | 2P |
| Control Units | No control units |
| Pilot Light | Without pilot light |
| Auxiliary Contacts | Without |
| Other Options | None |
| Electrical Connection | Lugs |
| Height | 10.00 in (254 mm) |
| Depth | 5.28 in (134 mm) |
| Width | 5.98 in (152 mm) |

Environment

| | |
|------------------------|---|
| Enclosure Type | NEMA 1 painted sheet steel surface none |
| Product Certifications | UL Listed[RETURN]CSA |

Ordering and shipping details

| | |
|-------------------|--------------|
| Category | US10CP121325 |
| Discount Schedule | 0CP1 |
| GTIN | 785901619581 |
| Returnability | No |
| Country of origin | US |

Packing Units

| | |
|------------------------------|------------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 6.00 in (15.24 cm) |
| Package 1 Width | 6.50 in (16.51 cm) |
| Package 1 Length | 11.50 in (29.21 cm) |
| Package 1 Weight | 6.44 lb(US) (2.921 kg) |
| Unit Type of Package 2 | PAL |
| Number of Units in Package 2 | 120 |

| | |
|------------------|---------------------------|
| Package 2 Height | 40.00 in (101.6 cm) |
| Package 2 Width | 40.00 in (101.6 cm) |
| Package 2 Length | 48.00 in (121.92 cm) |
| Package 2 Weight | 845.76 lb(US) (383.63 kg) |

Offer Sustainability

| | |
|-----------------------|--|
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Not compliant |
| China RoHS Regulation | China RoHS Declaration |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|