

# Product data sheet

## Characteristics

# 8903SPG2V03

Contactor, Type S, multipole lighting,  
electrically held, 60A, 3 pole, 220/240VAC  
50/60Hz coil, NEMA 1



## Main

Product	Electrically Held Lighting Contactor
Type	S

## Complementary

Control Circuit Voltage	240 V AC 60 Hz 220 V AC 50 Hz
Current Rating	60 A
Number of Poles	3P
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Other Options	None
Electrical Connection	Lugs
Height	12.68 in (322 mm)
Depth	6.02 in (153 mm)
Width	7.80 in (198 mm)

## Environment

Enclosure Type	NEMA 1 painted sheet steel surface none
Product Certifications	UL Listed[RETURN]CSA

## Ordering and shipping details

Category	US10CP121325
Discount Schedule	0CP1
GTIN	785901619475
Returnability	No
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.70 in (19.558 cm)
Package 1 Width	8.10 in (20.574 cm)
Package 1 Length	13.00 in (33.02 cm)
Package 1 Weight	12.00 lb(US) (5.443 kg)

Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Not compliant
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

Contractual warranty

Warranty	18 months
----------	-----------