

Product data sheet

Characteristics

8903SPO1V03

Contactor, Type S, multipole lighting,
electrically held, 60A, 2 pole, 220/240 VAC
50/60 Hz coil, open style



Main

Product	Electrically Held Lighting Contactor
Type	S

Complementary

Control Circuit Voltage	240 V AC 60 Hz 220 V AC 50 Hz
Current Rating	60 A
Number of Poles	2P
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Other Options	None
Electrical Connection	Lugs
Height	5.51 in (140 mm)
Depth	4.92 in (125 mm)
Width	4.33 in (110 mm)

Environment

Enclosure Type	Not rated (open device) surface none
Product Certifications	UL Listed CSA

Ordering and shipping details

Category	21325-8903 S (NOT S*C) ELECT.
Discount Schedule	CP1
GTIN	785901861843
Nbr. of units in pkg.	1
Package weight(Lbs)	5.50 lb(US) (2.495 kg)
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	5.51 in (14.0 cm)
Package 1 width	4.33 in (11.0 cm)
Package 1 Length	4.92 in (12.5 cm)

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------