

Product data sheet

Characteristics

8903SQG1V02

Contactor, Type S, multipole lighting,
electrically held, 100A, 2 pole, 110/120VAC
50/60Hz coil, NEMA 1



Main

Product	Electrically Held Lighting Contactor
Type	S

Complementary

Control Circuit Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Current Rating	100 A
Number of Poles	2P
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Other Options	None
Electrical Connection	Lugs
Height	25.16 in (639 mm)
Depth	8.98 in (228 mm)
Width	11.26 in (286 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel surface none
Product Certifications	UL Listed[RETURN]CSA

Ordering and shipping details

Category	US10CP121325
Discount Schedule	0CP1
GTIN	785901619444
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.60 in (26.924 cm)
Package 1 Width	12.00 in (30.48 cm)
Package 1 Length	25.70 in (65.278 cm)
Package 1 Weight	34.37 lb(US) (15.59 kg)

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Not compliant
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------