

Product data sheet

Characteristics

8903SQH2V02

lighting contactor, electrically held, 100 A, 3 pole, NEMA 3R, 120/110V 60/50Hz



Main

Product	Electrically Held Lighting Contactor
Type	S

Complementary

Control Circuit Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Current Rating	100 A
Number of Poles	3P
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Other Options	None
Electrical Connection	Lugs
Height	25.31 in (643 mm)
Depth	8.62 in (219 mm)
Width	12.83 in (326 mm)

Environment

Enclosure Type	NEMA 3R Stainless Steel surface none
Product Certifications	UL Listed CSA

Ordering and shipping details

Category	21325 - 8903 S (NOT S°C) ELECT.
Discount Schedule	CP1
GTIN	785901862758
Nbr. of units in pkg.	1
Package weight(Lbs)	9.75 lb(US) (4.42 kg)
Returnability	No
Country of origin	MX

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty

18 months
