

# Product data sheet

## Characteristics

# 8911DPSG13V06

Starter, Definite Purpose, nonreversing, 20A,  
3 pole, 3 phase, 440/480VAC 50/60Hz coil,  
melting alloy overload, NEMA 1



## Main

Product	Definite Purpose Starter
Ampere Rating	20 A
Horsepower Rating	3 Hp 230 V AC, 1 phase 7.5 Hp 230 V AC, 3 phase 1.5 Hp 115 V AC, 1 phase 7.5 Hp 460 V AC, 3 phase 7.5 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Circuit Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Phase	3 phase

## Complementary

Enclosure Material	Painted sheet steel
Enclosure Rating	NEMA 1
Locked Rotor Amperes	120 A 230 V AC 100 A 460 V AC 80 A 575 V AC
Number of Poles	3P
Range	DPS
Overload Type	Melting alloy
Number of Thermal Units	3

## Ordering and shipping details

Category	US10CP121381
Discount Schedule	OCP1
GTIN	785901024637
Returnability	Yes
Country of origin	US

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.30 in (18.542 cm)
Package 1 Width	8.60 in (21.844 cm)
Package 1 Length	13.30 in (33.782 cm)
Package 1 Weight	5.60 lb(US) (2.54 kg)

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------