

# Product data sheet

## Characteristics

# 8911DPSG32V02

Starter, Definite Purpose, nonreversing, 30A,  
2 pole, 1 phase, 110/120VAC 50/60Hz coil,  
melting alloy overload, NEMA 1



## Main

Product	Definite Purpose Starter
Ampere Rating	30 A
Horsepower Rating	2 Hp 115 V AC, 1 phase 5 hp 230 V AC, 1 phase
Maximum Voltage Rating	600 V AC
Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Phase	1 phase

## Complementary

Enclosure Material	Painted sheet steel
Enclosure Rating	NEMA 1
Locked Rotor Amperes	180 A 230 V AC 150 A 460 V AC 120 A 575 V AC
Number of Poles	2P
Range	DPS
Overload Type	Melting alloy
Number of Thermal Units	1




## Ordering and shipping details

Category	US10CP121381
Discount Schedule	0CP1
GTIN	785901002826
Returnability	Yes
Country of origin	US

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.30 in (16.002 cm)
Package 1 Width	7.00 in (17.78 cm)
Package 1 Length	11.40 in (28.956 cm)
Package 1 Weight	5.60 lb(US) (2.54 kg)

## Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------