

Product data sheet

Characteristics

8911DPSG32V09

Starter, Definite Purpose, nonreversing, 30A,
2 pole, 1 phase, 208V to 240V AC coil, melting
alloy overload, NEMA 1



Main

Product	Definite Purpose Starter
Ampere Rating	30 A
Horsepower Rating	2 Hp 115 V AC, 1 phase 5 hp 230 V AC, 1 phase
Maximum Voltage Rating	600 V AC
Control Circuit Voltage	220 V AC 50 Hz 208...240 V AC 60 Hz
Phase	1 phase

Complementary

Enclosure Material	Painted sheet steel
Enclosure Rating	NEMA 1
Locked Rotor Amperes	180 A 230 V AC 150 A 460 V AC 120 A 575 V AC
Number of Poles	2P
Range	DPS
Overload Type	Melting alloy
Number of Thermal Units	1

Ordering and shipping details

Category	US10CP121381
Discount Schedule	0CP1
GTIN	785901024699
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.60 in (16.764 cm)
Package 1 Width	7.10 in (18.034 cm)
Package 1 Length	11.20 in (28.448 cm)
Package 1 Weight	5.75 lb(US) (2.608 kg)

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------