

# Product data sheet

## Characteristics

# 8911DPSG52V09

Starter, Definite Purpose, nonreversing, 50A,  
2 pole, 1 phase, 208V to 240V AC coil, melting  
alloy overload, NEMA 1



## Main

Product	Definite Purpose Starter
Ampere Rating	50 A
Horsepower Rating	3 Hp 115 V AC, 1 phase 10 hp 230 V AC, 1 phase
Maximum Voltage Rating	600 V AC
Control Circuit Voltage	220 V AC 50 Hz 208...240 V AC 60 Hz
Phase	1 phase

## Complementary

Enclosure Material	Painted sheet steel
Enclosure Rating	NEMA 1
Locked Rotor Amperes	300 A 230 V AC 250 A 460 V AC 200 A 575 V AC
Number of Poles	2P
Range	DPS
Overload Type	Melting alloy
Number of Thermal Units	1




## Ordering and shipping details

Category	US10CP121381
Discount Schedule	OCP1
GTIN	785901024835
Returnability	Yes
Country of origin	US

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.70 in (19.558 cm)
Package 1 Width	8.80 in (22.352 cm)
Package 1 Length	13.50 in (34.29 cm)
Package 1 Weight	9.34 lb(US) (4.237 kg)

## Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------