

# Product data sheet

## Characteristics

# 8911DPSO53V09

NEMA Starter, Definite Purpose, 50A, 30HP at 600VAC, 3 phase, 3 pole, melting alloy, 208V to 240VAC coil, open



## Main

Product	Definite Purpose Starter
Ampere Rating	50 A
Horsepower Rating	3 Hp 115 V AC, 1 phase 10 Hp 230 V AC, 1 phase 15 Hp 230 V AC, 3 phase 30 Hp 460 V AC, 3 phase 30 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Circuit Voltage	220 V AC 50 Hz 208...240 V AC 60 Hz
Phase	3 phase

## Complementary

Enclosure Rating	Not rated (open device)
Locked Rotor Amperes	300 A 230 V AC 250 A 460 V AC 200 A 575 V AC
Number of Poles	3P
Range	DPS
Overload Type	Melting alloy
Number of Thermal Units	3




## Ordering and shipping details

Category	US10CP121381
Discount Schedule	0CP1
GTIN	785901025207
Returnability	Yes
Country of origin	US

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.30 in (13.462 cm)
Package 1 Width	4.80 in (12.192 cm)
Package 1 Length	8.00 in (20.32 cm)
Package 1 Weight	2.94 lb(US) (1.334 kg)

## Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------