



### Main

Product	Well-Guard Control
Type	Class 8940 type R
Device Application	Pumping

### Complementary

Control Circuit Type	Common control circuit
Control Circuit Voltage	480 V AC 60 Hz 440 V AC 50 Hz
Line Rated Current	270 A
Number of Poles	3
Horsepower Rating	200 hp 480 V AC, 3 phase
Maximum Voltage Rating	480 V AC
Control Units	Selector switch (HAND-OFF-AUTO) Push-button (START)
Disconnect Type	Fusible disconnect switch
Associated fuse rating	400 A
Fuse type	H or K
Thermal overload type	Motor Logic solid state class 10/20
Protection Type	Overload Phase loss Phase unbalance
Device mounting	Surface
Electrical Connection	Screw terminal
NEMA size	6
Height	92.99 in (2362 mm)
Width	35.98 in (914 mm)
Depth	19.25 in (489 mm)

### Environment

NEMA Rating	NEMA 3R
Enclosure type	Weatherproof enclosure indoor/outdoor
Product Certifications	UL Listed NEMA


### Ordering and shipping details

Category	21394-8940 M,P,R,V
Discount Schedule	CP1
GTIN	785901716983
Returnability	No
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	92.99 in (236.2 cm)
Package 1 Width	35.98 in (91.4 cm)
Package 1 Length	19.25 in (48.9 cm)
Package 1 Weight	875.00 lb(US) (396.893 kg)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Under investigation
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------