

# Product data sheet

## Characteristics

# 8940SSF4100V02G45S

Pump Panel, NEMA Type S, Well Guard, Size 4, 135A, 10kA SSCR, 100HP, 200A Class H and K fuse clip, Motor Logic SSOLR, 120VAC 60Hz coil, NEMA 3R



### Main

Product	Well-Guard Control
Type	class 8940 type SS
Device Application	Pumping

### Complementary

Control Circuit Type	Separate control circuit
Control Circuit Voltage	480 V AC 60 Hz 440 V AC 50 Hz
Line Rated Current	135 A
Number of Poles	3
Horsepower Rating	100 hp 480 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Selector switch HAND-OFF-AUTO) Push-button START)
Disconnect Type	Fusible disconnect switch
Associated fuse rating	200 A
Fuse type	H or K
Thermal overload type	Motor Logic solid state class 10/20
Protection Type	Overload Phase loss Phase unbalance
Device mounting	Surface
Electrical Connection	Screw terminal
NEMA size	4
Height	49.02 in (1245 mm)
Width	20.6 in (522 mm)
Depth	10.4 in (263 mm)

### Environment

NEMA Rating	NEMA 3R
Enclosure type	Weatherproof enclosure indoor/outdoor
Product Certifications	UL Listed[RETURN]NEMA

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Ordering and shipping details

Category	US10CP121389
Discount Schedule	0CP1
GTIN	785901415220
Returnability	No
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.0 in (33.0 cm)
Package 1 Width	23.0 in (58.4 cm)
Package 1 Length	51.0 in (129.5 cm)
Package 1 Weight	141.001 lb(US) (63.957 kg)

## Offer Sustainability

California proposition 65	"WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> "
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Not compliant
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
PVC free	Yes

## Contractual warranty

Warranty	18 months
----------	-----------