

# Product data sheet

## Characteristics

# 8940SSF4100V06

Pump Panel, NEMA Type S, Well Guard, Size 4, 135A, 10kA SSCR, 100HP, 200A Class H and K fuse clip, Motor Logic SSOLR, 480VAC 60Hz coil, NEMA 3R



### Main

Product	Well-Guard Control
Type	class 8940 type SS
Device Application	Pumping

### Complementary

Control Circuit Type	Common control circuit
Control Circuit Voltage	480 V AC 60 Hz 440 V AC 50 Hz
Line Rated Current	135 A
Number of Poles	3
Horsepower Rating	100 hp 480 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Selector switch HAND-OFF-AUTO) Push-button START)
Disconnect Type	Fusible disconnect switch
Associated fuse rating	200 A
Fuse type	H or K
Thermal overload type	Motor Logic solid state class 10/20
Protection Type	Overload Phase loss Phase unbalance
Device mounting	Surface
Electrical Connection	Screw terminal
NEMA size	4
Height	49.02 in (1245 mm)
Width	20.6 in (522 mm)
Depth	10.4 in (263 mm)

### Environment

NEMA Rating	NEMA 3R
Enclosure type	Weatherproof enclosure indoor/outdoor
Product Certifications	UL Listed[RETURN]NEMA

### Ordering and shipping details

Category	US10CP121389
Discount Schedule	OCP1
GTIN	785901125518
Returnability	Yes

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	49.02 in (124.5 cm)
Package 1 Width	20.6 in (52.2 cm)
Package 1 Length	10.4 in (26.3 cm)
Package 1 Weight	147.000 lb(US) (66.678 kg)

## Offer Sustainability

California proposition 65	"WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> "
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Not compliant
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
PVC free	Yes

## Contractual warranty

Warranty	18 months
----------	-----------