

# Product data sheet

## Characteristics

# 8940WF3S2V06A28H30

Pump Panel, NEMA Type S, Well Guard, oil field, Size 4, 135A, 100HP, 200A fusible disconnect, Motor Logic SSOLR, 440/480VAC 50/60Hz coil, NEMA 3R



### Main

Product	Well-Guard Control
Type	S2
Device Application	Pumping

### Complementary

Control Circuit Type	Common control circuit
Control Circuit Voltage	480 V AC 60 Hz 440 V AC 50 Hz
Line Rated Current	135 A
Number of Poles	3
Horsepower Rating	100 hp 480 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Selector switch HAND-OFF-AUTO) Push-button START)
Disconnect Type	Fusible disconnect switch
Associated fuse rating	400 A
Fuse type	H or K
Thermal overload type	Motor Logic solid state class 10/20
Protection Type	Overload Phase loss Phase unbalance
Device mounting	Surface
Electrical Connection	Screw terminal
NEMA size	4
Height	56.5 in (1435 mm)
Width	24.5 in (622 mm)
Depth	10.3 in (262 mm)

### Environment

NEMA Rating	NEMA 3R
Enclosure type	Weatherproof enclosure indoor/outdoor
Product Certifications	UL Listed[RETURN]NEMA

### Ordering and shipping details

Category	US10CP121397
Discount Schedule	0CP1
GTIN	785901466918
Returnability	No

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	56.5 in (143.5 cm)
Package 1 Width	24.5 in (62.2 cm)
Package 1 Length	10.3 in (26.2 cm)
Package 1 Weight	175.0009 lb(US) (79.379 kg)

## Offer Sustainability

California proposition 65	"WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> "
EU RoHS Directive	Under investigation

## Contractual warranty

Warranty	18 months
----------	-----------