

# Product data sheet

## Characteristics

# 9050AO10EV02

Timing Relay, Type A, pneumatic, on delay, 0.1 to 60 seconds, 15A, 600V, SPDT, timed, 110/120VAC 50/60Hz coil, open



## Main

Product Range	9050A/H
Product Type	Timer
Timing Mode	On-delay
Timing Range	0.1 s...1 min
Switch Function	SPDT
Coil Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Contact Operation	Time delayed 1 NO + 1 NC
Current rating	15 A

## Complementary

Maximum switching voltage	600 V AC
Electrical connection	Screw-clamp terminals
Reset response time	29 Ms - on-delay 27 ms - off-delay
Mounting Support	Panel

## Environment

Ambient Temperature Range - Operational	68...104 °F (20...40 °C)
Certifications	UL Listed[RETURN]CSA
Height	2.64 in (67 mm)
Width	4.02 in (102 mm)
Depth	4.37 in (111 mm)



## Ordering and shipping details

Category	US10CP121631
Discount Schedule	OCP1
GTIN	785901864318
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.50 in (8.9 cm)
Package 1 Width	4.88 in (12.4 cm)
Package 1 Length	6.69 in (17.0 cm)
Package 1 Weight	26.72 oz (757.5 g)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>

## Contractual warranty

Warranty	18 months
----------	-----------