

Product data sheet

Characteristics

9065SEO12

Overload Relay, Type S, melting alloy,
separate mount overload, NEMA size 3, 3 pole,
3 phase, 86A, 600VAC



Main

Range of Product	S
Product destination	Starter
Thermal overload type	Melting alloy

Complementary

NEMA size	3
Number of thermal units required	3
Mounting Support	Panel
Product or Component Type	Overload relay
[Ue] rated operational voltage	600 V AC
Height	5.59 in (142.1 mm)
Width	5.31 in (134.9 mm)
Depth	5.75 in (146.1 mm)

Ordering and shipping details

Category	US10CP121661
Discount Schedule	0CP1
GTIN	785901788522
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.40 in (16.256 cm)
Package 1 Width	6.70 in (17.018 cm)
Package 1 Length	8.40 in (21.336 cm)
Package 1 Weight	3.42 lb(US) (1.551 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Not compliant
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------