



### Main

|         |             |
|---------|-------------|
| Range   | 9080FB      |
| Product | Fuse holder |

### Complementary

|                                |  |
|--------------------------------|--|
| Current Rating                 | 30 A   |
| [Ue] rated operational voltage | <= 600 V AC/DC   |
| Fuse type                      | CC   |
| Fuse size                      | 0.4063 x 1.5 in  |
| Number of poles                | 1  |
| Electrical Connection          | Pressure wire clamp  |
| Wire Gauge                     | AWG 14...AWG 10 copper or aluminium  |
| SCCR                           | 200 kA UL 512  |
| Product Certifications         | UL recognized E40747 CCN IZLT2[RETURN]CSA file 70360 class 6225 01[RETURN]CE |
| Operating Temperature          | -40...257 °F (-40...125 °C)  |
| Mounting Type                  | Surface mount  |
| Block Material                 | Thermoplastic: block   |
| Wire stripping length          | 0.4375 in (11.11 mm)   |
| Terminal Tightening Torque     | Screw terminals 25 lbf.in (2.82 N.m) AWG 14...AWG 10 copper                  |
| Height                         | 3.13 in (79.50 mm)   |
| Width                          | 0.85 in (21.59 mm)   |
| Depth                          | 1.29 in (32.77 mm)   |

### Ordering and shipping details

|                   |              |
|-------------------|--------------|
| Category          | US10CP121701 |
| Discount Schedule | OCP1         |
| GTIN              | 785901097198 |
| Returnability     | Yes          |
| Country of origin | US           |

### Packing Units

|                              |                    |
|------------------------------|--------------------|
| Unit Type of Package 1       | PCE                |
| Number of Units in Package 1 | 1                  |
| Package 1 Height             | 0.90 in (2.286 cm) |
| Package 1 Width              | 1.40 in (3.556 cm) |
| Package 1 Length             | 3.10 in (7.874 cm) |
| Package 1 Weight             | 1.44 oz (40.823 g) |
| Unit Type of Package 2       | CAR                |

|                              |                        |
|------------------------------|------------------------|
| Number of Units in Package 2 | 50                     |
| Package 2 Height             | 3.90 in (9.906 cm)     |
| Package 2 Width              | 6.90 in (17.526 cm)    |
| Package 2 Length             | 9.70 in (24.638 cm)    |
| Package 2 Weight             | 4.58 lb(US) (2.077 kg) |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| California proposition 65  | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>   |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a>   |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>  |
| RoHS exemption information | <a href="#">Yes</a>   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|