



Main

Range	9080FB
Product	Fuse holder

Complementary

Current Rating	30 A
[Ue] rated operational voltage	<= 600 V AC/DC
Fuse type	CC
Fuse size	0.4063 x 1.5 in
Number of poles	3
Electrical Connection	Pressure wire clamp
Wire Gauge	AWG 14...AWG 10 copper or aluminium
SCCR	200 kA UL 512
Product Certifications	CE[RETURN]UL recognized E40747 CCN IZLT2[RETURN]CSA file 70360 class 6225 01
Operating Temperature	-40...257 °F (-40...125 °C)
Mounting Type	Surface mount
Block Material	Thermoplastic: block
Wire stripping length	0.4375 in (11.11 mm)
Terminal Tightening Torque	Screw terminals 25 lbf.in (2.82 N.m) AWG 14...AWG 10 copper
Height	3.13 in (79.50 mm)
Width	2.35 in (59.69 mm)
Depth	1.29 in (32.77 mm)

Ordering and shipping details

Category	US10CP121701
Discount Schedule	0CP1
GTIN	785901097211
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.30 in (3.302 cm)
Package 1 Width	2.40 in (6.096 cm)
Package 1 Length	3.10 in (7.874 cm)
Package 1 Weight	3.84 oz (108.862 g)
Unit Type of Package 2	CAR

Number of Units in Package 2	20
Package 2 Height	3.30 in (8.382 cm)
Package 2 Width	7.80 in (19.812 cm)
Package 2 Length	13.00 in (33.02 cm)
Package 2 Weight	5.38 lb(US) (2.44 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------