

9080FB3611J

Fuse holder, Square D 9080FB, max 30A rated, 600VAC/DC, Class J type fuses, 3 pole, surface mount



Main

| | |
|---------|-------------|
| Range | 9080FB |
| Product | Fuse holder |

Complementary

| | |
|--------------------------------|--|
| Current Rating | 30 A |
| [Ue] rated operational voltage | <= 600 V AC/DC |
| Fuse type | J |
| Fuse size | 0.8125 x 2.25 in |
| Number of poles | 3 |
| Electrical Connection | Box lugs |
| Wire Gauge | AWG 14...AWG 2 copper or aluminium |
| SCCR | 200 kA UL 512 |
| Product Certifications | CSA file 70360 class 6225 01[RETURN]CE[RETURN]UL listed file E40747 CCN IZLT |
| Operating Temperature | -40...257 °F (-40...125 °C) |
| Mounting Type | Surface mount |
| Block Material | Thermoplastic: block |
| Wire stripping length | 0.4375 in (11.11 mm) |
| Terminal Tightening Torque | Screw terminals 25 lbf.in (2.82 N.m) AWG 14...AWG 6 copper |
| Height | 4.07 in (103.38 mm) |
| Width | 4.72 in (119.89 mm) |
| Depth | 2.09 in (53.09 mm) |

Ordering and shipping details

| | |
|-------------------|--------------|
| Category | US10CP121701 |
| Discount Schedule | OCP1 |
| GTIN | 785901139638 |
| Returnability | No |
| Country of origin | US |

Packing Units

| | |
|------------------------------|---------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 2.00 in (5.08 cm) |
| Package 1 Width | 3.30 in (8.382 cm) |
| Package 1 Length | 3.40 in (8.636 cm) |
| Package 1 Weight | 5.60 oz (158.757 g) |

| | |
|------------------------------|------------------------|
| Unit Type of Package 2 | CAR |
| Number of Units in Package 2 | 20 |
| Package 2 Height | 4.40 in (11.176 cm) |
| Package 2 Width | 9.90 in (25.146 cm) |
| Package 2 Length | 17.50 in (44.45 cm) |
| Package 2 Weight | 8.01 lb(US) (3.633 kg) |

Offer Sustainability

| | |
|----------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|