



Main

Range	9080FB
Product	Fuse holder

Complementary

Current Rating	100 A
[Ue] rated operational voltage	<= 600 V AC/DC
Fuse type	R
Fuse size	1 x 7.875 in
Number of poles	3
Electrical Connection	Box lugs
Wire Gauge	AWG 6...AWG 2/0 copper or aluminium
SCCR	200 kA UL 512
Product Certifications	UL listed file E40747 CCN IZLT[RETURN]CSA file 70360 class 6225 01[RETURN]CE
Operating Temperature	-40...302 °F (-40...150 °C)
Mounting Type	Surface mount
Block Material	Phenolic: block
Wire stripping length	1.3125 in (33.34 mm)
Terminal Tightening Torque	Lugs 40 lbf.in (4.52 N.m) AWG 8 copper or aluminium Lugs 35 lbf.in (3.95 N.m) AWG 14 copper Lugs 120 lbf.in (13.56 N.m) AWG 6...AWG 2/0 copper or aluminium Lugs 35 lbf.in (3.95 N.m) AWG 12...AWG 10 copper or aluminium
Height	8.12 in (206.25 mm)
Width	5.73 in (145.54 mm)
Depth	2.6 in (66.04 mm)

Ordering and shipping details

Category	US10CP121701
Discount Schedule	OCP1
GTIN	785901097266
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.50 in (6.35 cm)
Package 1 Width	6.00 in (15.24 cm)
Package 1 Length	8.10 in (20.574 cm)
Package 1 Weight	34.08 oz (966.152 g)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------