

Product data sheet

Characteristics

9421V2A30

Manual Motor Switch, TeSys Vario, rotary handle, 25A, 3 pole, 10HP at 480V, metallic enclosure, UL Type 12



Main

Color	Red/yellow
Enclosure type	Dust and damp proof enclosure indoor
Lock type	Padlockable
Range of Product	VARIO

Complementary

Line Rated Current	25 A
Auxiliary contact composition	Without
Depth	6.25 in (158.75 mm)
Device mounting	Surface
Enclosure material	Metallic metal
Height	7.38 in (187.45 mm)
Maximum Horse Power Rating	5 Hp 240 V AC 10 Hp 480 V AC 15 hp 600 V AC
Permissible voltage	600 V AC
Width	5.5 in (139.70 mm)

Environment

NEMA Degree of Protection	NEMA 12
Product Certifications	UL listed file E164864 CCN NLRV[RETURN]CSA LR81630 class 3211 05


Ordering and shipping details

Category	US10CP121730
Discount Schedule	0CP1
GTIN	785901058939
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.00 in (15.24 cm)
Package 1 Width	7.00 in (17.78 cm)
Package 1 Length	8.00 in (20.32 cm)
Package 1 Weight	7.24 lb(US) (3.285 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Under investigation
China RoHS Regulation	 China RoHS Declaration
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------