

Product data sheet

Characteristics

9422A1

Operating mechanism, flange mounted,
variable depth, handle mechanism, 6in handle,
NEMA 1, 3R, 4, 12 enclosure

Main

Product	Handle Mechanism
For Use With	Disconnect switches (30...200 A) All circuit breaker mechanisms



Complementary

Product Type	Variable depth
Product destination	All circuit breaker mechanisms Disconnect switches (30...200 A)
Enclosure Types	NEMA 1/3/3R/4/12 enclosures
Handle Length	6 in (152.40 mm)
Net Weight	2.78 lb(US) (1.26 kg)

Ordering and shipping details

Category	US10CP121732
Discount Schedule	0CP1
GTIN	785901739739
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.80 in (4.572 cm)
Package 1 Width	3.90 in (9.906 cm)
Package 1 Length	9.60 in (24.384 cm)
Package 1 Weight	2.78 lb(US) (1.261 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	300
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	840.00 lb(US) (381.017 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Approximate Dimensions

