


9422ATDF632

Operating mechanism, flange mounted,
variable depth, 60A, 600V, fuseholder, switch
mechanism, 6 inch handle, NEMA 4X



Main

Range	9422T
Product	Disconnect Switch
Disconnect Type	Fusible disconnect switch

Complementary

Mounting Type	Flange rod variable depth
Current Rating	60 A
Horsepower Rating	15 Hp 200 V AC 15 Hp 230 V AC 30 Hp 460 V AC 50 Hp 575 V AC 10 hp 250 V DC
Fuse Rating	60 A 600 V
Handle Type	6 in handle included NEMA 4/4X enclosures Stainless Steel
Fuse Type	J K R H

Environment

Certifications	UL Recognized[RETURN]CSA
----------------	--------------------------



Ordering and shipping details

Category	US10CP121732
Discount Schedule	OCP1
GTIN	785901353201
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.00 in (5.08 cm)
Package 1 Width	4.00 in (10.16 cm)
Package 1 Length	9.00 in (22.86 cm)
Package 1 Weight	14.72 lb(US) (6.679 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------