

# 9422BTCN30

Operating mechanism, flange mounted, fixed depth assembly, 30A, 600 V, no fuse, switch mechanism, 6 inch handle



## Main

Range	9422T
Product	Disconnect Switch
Disconnect Type	Non-fusible disconnect switch

## Complementary

Mounting Type	Bracket fixed depth
Current Rating	30 A
Horsepower Rating	7.5 Hp 200 V AC 7.5 Hp 230 V AC 15 Hp 460 V AC 20 Hp 575 V AC 5 hp 250 V DC
Handle Type	6 in handle included

## Environment

Certifications	UL Recognized[RETURN]CSA
----------------	--------------------------



## Ordering and shipping details

Category	US10CP121732
Discount Schedule	0CP1
GTIN	785901872290
Returnability	No
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.20 in (33.528 cm)
Package 1 Width	8.40 in (21.336 cm)
Package 1 Length	12.20 in (30.988 cm)
Package 1 Weight	9.64 lb(US) (4.373 kg)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
PVC free	Yes

## Contractual warranty

Warranty	18 months
----------	-----------