

# 9422BTDF62

Operating mechanism, flange mounted, fixed depth assembly, 60A, 600 V, fuseholder, switch mechanism, 6 inch handle



## Main

|                 |                           |
|-----------------|---------------------------|
| Range           | 9422T                     |
| Product         | Disconnect Switch         |
| Disconnect Type | Fusible disconnect switch |

## Complementary

|                   |                                                                                        |
|-------------------|----------------------------------------------------------------------------------------|
| Mounting Type     | Bracket fixed depth                                                                    |
| Current Rating    | 60 A                                                                                   |
| Horsepower Rating | 15 Hp 200 V AC<br>15 Hp 230 V AC<br>30 Hp 460 V AC<br>50 Hp 575 V AC<br>10 hp 250 V DC |
| Fuse Rating       | 60 A 600 V                                                                             |
| Handle Type       | 6 in handle included                                                                   |
| Fuse Type         | J                                                                                      |

## Environment

|                |                          |
|----------------|--------------------------|
| Certifications | UL Recognized[RETURN]CSA |
|----------------|--------------------------|

## Ordering and shipping details

|                   |              |
|-------------------|--------------|
| Category          | US10CP121732 |
| Discount Schedule | 0CP1         |
| GTIN              | 785901162629 |
| Returnability     | No           |
| Country of origin | MX           |

## Packing Units

|                              |                         |
|------------------------------|-------------------------|
| Unit Type of Package 1       | PCE                     |
| Number of Units in Package 1 | 1                       |
| Package 1 Height             | 13.00 in (33.02 cm)     |
| Package 1 Width              | 8.50 in (21.59 cm)      |
| Package 1 Length             | 12.00 in (30.48 cm)     |
| Package 1 Weight             | 17.26 lb(US) (7.831 kg) |

## Offer Sustainability

|                            |                                                                                                                                                                                                                                                                                             |
|----------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| California proposition 65  | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                           |
| EU RoHS Directive          | Compliant with Exemptions                                                                                                                                                                                                                                                                   |
| Mercury free               | Yes                                                                                                                                                                                                                                                                                         |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                                                                                                                                                                                                                                      |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                                                         |
| PVC free                   | Yes                                                                                                                                                                                                                                                                                         |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|