



Main

Range	9422T
Product	Disconnect Switch
Disconnect Type	Non-fusible disconnect switch

Complementary

Mounting Type	Flange rod variable depth
Current Rating	100 A
Horsepower Rating	25 Hp 200 V AC 30 Hp 230 V AC 60 Hp 460 V AC 75 Hp 575 V AC 20 hp 250 V DC
Handle Type	Ordered separately

Environment

Certifications	UL Recognized[RETURN]CSA
----------------	--------------------------

Ordering and shipping details

Category	US10CP121732
Discount Schedule	0CP1
GTIN	785901879824
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.10 in (18.034 cm)
Package 1 Width	11.20 in (28.448 cm)
Package 1 Length	16.00 in (40.64 cm)
Package 1 Weight	6.36 lb(US) (2.885 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------