



Main

Product Range	Type S
Component type	Push-button
Used with	Contactor starter

Complementary

NEMA size	1 00 2 0 3
Marking	START-STOP
Mounting Mode	Panel-mounted
Rated breaking capacity	3 A 120 V AC inductive control circuit UL 508 1.5 A 240 V AC inductive control circuit UL 508 0.6 A 600 V AC inductive control circuit UL 508 5 A 600 V AC resistive control circuit UL 508
Height	1.02 in (25.8 mm)
Width	2.58 in (65.5 mm)
Depth	24.00 in (609.6 mm)
Net Weight	0.37 lb(US) (0.17 kg)

Environment

NEMA Degree of Protection	NEMA 1
Product Certifications	CSA[RETURN]UL Listed[RETURN]UL Recognized


Ordering and shipping details

Category	US10CP121761
Discount Schedule	OCP1
GTIN	785901867234
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.81 in (4.6 cm)
Package 1 Width	3.90 in (9.9 cm)
Package 1 Length	5.79 in (14.7 cm)
Package 1 Weight	6.08 oz (172.4 g)

Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
EU RoHS Directive	Under investigation
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------