

Main

| | |
|----------------|-------------------|
| Product Range | Type S |
| Component type | Push-button |
| Used with | Contactor starter |

Complementary

| | |
|-------------------------|---|
| NEMA size | 2 0 6 4 5 3 7 00 1 |
| Marking | START-STOP ON-OFF |
| Mounting Mode | Panel-mounted |
| Rated breaking capacity | 6 A 120 V AC inductive control circuit UL 508 3 A 240 V AC inductive control circuit UL 508 1.2 A 600 V AC inductive control circuit UL 508 10 A 600 V AC resistive control circuit UL 508 1.1 A 125 V DC resistive control circuit UL 508 0.55 A 250 V DC resistive control circuit UL 508 0.2 A 600 V DC resistive control circuit UL 508 |

Environment

| | |
|---------------------------|--------------------------|
| NEMA Degree of Protection | NEMA 1 NEMA 12/3R |
| Product Certifications | UL Recognized[RETURN]CSA |


Ordering and shipping details

| | |
|-------------------|--------------|
| Category | US10CP121761 |
| Discount Schedule | OCP1 |
| GTIN | 785901030171 |
| Returnability | Yes |
| Country of origin | MX |

Packing Units

| | |
|------------------------------|--------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3.39 in (8.6 cm) |
| Package 1 Width | 4.41 in (11.2 cm) |
| Package 1 Length | 6.50 in (16.5 cm) |
| Package 1 Weight | 16.48 oz (467.2 g) |

Offer Sustainability

| | |
|---------------------------|--|
| California proposition 65 | WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov |
| EU RoHS Directive | Under investigation |
| China RoHS Regulation |  China RoHS Declaration |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|