



### Main

Product Range	Type S
Component type	Selector switch
Used with	Contactor starter

### Complementary

NEMA size	00 1 0 2 3
Marking	HAND-OFF-AUTO
Mounting Mode	Panel-mounted
Rated breaking capacity	3 A 120 V AC inductive control circuit UL 508 1.5 A 240 V AC inductive control circuit UL 508 0.6 A 600 V AC inductive control circuit UL 508 5 A 600 V AC resistive control circuit UL 508
Height	1.88 in (47.75 mm)
Width	3.81 in (96.77 mm)
Depth	5.63 in (143.00 mm)
Net Weight	0.51 lb(US) (0.23 kg)

### Environment

NEMA Degree of Protection	NEMA 1
Product Certifications	UL Listed[RETURN]UL Recognized[RETURN]CSA


### Ordering and shipping details

Category	US10CP121761
Discount Schedule	OCP1
GTIN	785901783008
Returnability	Yes
Country of origin	MX

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.01 in (5.1 cm)
Package 1 Width	3.90 in (9.9 cm)
Package 1 Length	5.91 in (15.0 cm)
Package 1 Weight	6.72 oz (190.5 g)

Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Under investigation
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

Contractual warranty

Warranty	18 months
----------	-----------