



Main

Product Range	Type S
Component type	Selector switch
Used with	Contactor starter

Complementary

NEMA size	00 0 2 1 3
Marking	ON-OFF
Mounting Mode	Panel-mounted
Rated breaking capacity	3 A 120 V AC inductive control circuit UL 508 1.5 A 240 V AC inductive control circuit UL 508 0.6 A 600 V AC inductive control circuit UL 508 5 A 600 V AC resistive control circuit UL 508

Environment

NEMA Degree of Protection	NEMA 1
Product Certifications	UL Listed[RETURN]CSA[RETURN]UL Recognized


Ordering and shipping details

Category	US10CP121761
Discount Schedule	OCP1
GTIN	785901783022
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.09 in (5.3 cm)
Package 1 Width	3.90 in (9.9 cm)
Package 1 Length	5.91 in (15.0 cm)
Package 1 Weight	8.16 oz (231.3 g)

Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
EU RoHS Directive	Under investigation
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------