


AK5JB143

Busbar, Linergy HK, 160A, 4 conductors,
L344mm, for mounting in enclosure W600mm



Main

Range	Linergy
Product name	HK
Product or Component Type	Busbar
Device Application	Distribution
Tap-offs (18 mm)	12
Bar length	13.54 in (344 mm)
Enclosure/cubicle width	600 mm
Network type	AC
[Ie] rated operational current	160 A 95 °F (35 °C)
[Ue] rated operational voltage	400 V off-load plugging-in and unplugging, with supply switched on)IEC 60439-1 480 V off-load plugging-in and unplugging, with supply switched on)CSA 480 V off-load plugging-in and unplugging, with supply switched on)UL 600 V plugging-in and unplugging, with supply switched off)CSA 600 V plugging-in and unplugging, with supply switched off)UL 690 V plugging-in and unplugging, with supply switched off)IEC 60439-1
Number of conductors	4

Complementary

Bar width	1.77 in (45 mm)
Width	3.19 in (81 mm)
Depth	3.23 in (82 mm)
Network Frequency	50/60 Hz
[Ui] rated insulation voltage	600 V CSA 600 V UL 690 V IEC 60439-1
Peak current	25 kA
I ² t on activation	10000000 A ² .s
Protection type	AM fuses In = 160 A, I _{sc} = 100 kA, I _e = 160 A GF fuses In = 160 A, I _{sc} = 100 kA, I _e = 160 A NS160H circuit breaker In = 160 A, I _{sc} = 36 kA, I _e = 160 A NS160H circuit breaker In = 160 A, I _{sc} = 70 kA, I _e = 160 A
Connections - terminals	Connector 0.00...0.11 in ² (2.5...70 mm ²) flexible with cable end Connector 0.00...0.11 in ² (2.5...70 mm ²) rigid
Tightening torque	88.51 lbf.in (10 N.m)
Mounting position	Vertical using side stop AK5BT01 on mounting plates AK5PA Horizontal
Flame retardance	V0 conforming to UL 94
Net Weight	1.54 lb(US) (0.7 kg)

Environment

Standards	IEC 60439
Product Certifications	CSA[RETURN]UL[RETURN]LROS (Lloyds register of shipping)[RETURN]DNV
IP degree of protection	IPxx B conforming to IEC 60529
Fire resistance	1562 °F (850 °C) IEC 60695

Ordering and shipping details

Category	US10I1122623
Discount Schedule	0I11
GTIN	3389110576771
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.33 in (11.000 cm)
Package 1 Width	4.33 in (11.000 cm)
Package 1 Length	20.67 in (52.500 cm)
Package 1 Weight	34.46 oz (977.000 g)
Unit Type of Package 2	P06
Number of Units in Package 2	30
Package 2 Height	29.53 in (75.000 cm)
Package 2 Width	23.62 in (60.000 cm)
Package 2 Length	31.50 in (80.000 cm)
Package 2 Weight	93.28 lb(US) (42.310 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------