



### Main

Product or Component Type	Straight length
Range of Product	I-Line

### Complementary

Line Rated Current	2000 A
Short Circuit Rating	125 kA
Busbar Material	Aluminium busbar
Integral Ground	50 percent capacity integral ground bus
Rated Voltage	600 V AC
Number of Phases	3 phase
Wiring configuration	3-wire
Length	10 ft (3.05 m)

### Environment

Product Certifications	UL listed file E22182
Standards	CSA C22.2 No 27:1997 IEC 61439-2 UL 857

### Ordering and shipping details

Category	20330-AP2/AR2 2000A 3WIRE-INDL
Discount Schedule	PE8
GTIN	785901061410
Number of Units in Package 1	1
Package 1 Weight	1 lb(US) (0.45 kg)
Returnability	Yes
Country of origin	US

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
PVC free	Yes

### Contractual warranty

Warranty	18 months
----------	-----------