



Main

Range	Acti9
Device short name	MSC 18
Product or Component Type	Chassis
Device Application	Distribution

Complementary

Range compatibility	Acti9 Acti9 Isobar B distribution board
Line Rated Current	250 A
Rated voltage	415 V AC 50 Hz
Short-circuit withstand	25 kA 0.1 s
[Icw] rated short-time withstand current	25 kA
[Ui] Rated Insulation Voltage	500 V
[Uimp] rated impulse withstand voltage	6 kV
Number of ways	1 way in(omer) - 3P 24 ways outgoer)
Outgoer Pole capacity	24 x 0.71 in (18 mm)
Length	8.58 in (218 mm)
Width	8.46 in (215 mm)

Environment

Standards	AS/NZS 61439
-----------	--------------

Ordering and shipping details

Category	US10DE200908
Discount Schedule	0DE2
GTIN	9321243001083
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.74 in (9.5 cm)
Package 1 Width	9.45 in (24.0 cm)
Package 1 Length	20.00 in (50.8 cm)
Package 1 Weight	4.75 lb(US) (2.154 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations