

Main

Range	I-Line
Product Type	Panelboard
Lighting Section Type	NF
Provided Equipment	Neutral bar aluminium)
Circuit Breaker Type	LI FC QB LA/LH QG FA JD/JG/JJ/JL EDB/EGB/EJB LD LG HD/HG/HJ/HL PK LJ QJ LL QD Q4

Complementary

Rated Current	400 A
Lighting Section Current	250 A
Rated Operational Voltage	600Y/347 V AC 48 V DC
Breaking Capacity	10...200 KA main 18...65 kA branch
Main Type	Main lugs Main breaker
Lighting Section Number of Circuits	42
Number of Phases	3 phase
Height	86 in (2184.4 mm)
Width	26 in (660.4 mm)
Depth	9.5 in (241.3 mm)

Environment

NEMA Rating	NEMA 3R/5/12 NEMA 1
Certifications	UL Listed[RETURN]CE[RETURN]cULus

Ordering and shipping details

Category	US1PE1A08310
Discount Schedule	PE1A
GTIN	3606481029911
Returnability	No
Country of origin	US

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	25.0004 lb(US) (11.34 kg)

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------