

DFCC1V

Fuse carrier, TeSys DF, 1P, 30A, 600VAC,
fuse class CC, blown fuse indicator

Main

Range	TeSys
Product name	TeSys DF
Product or Component Type	Fuse carrier
Device short name	DFCC
Poles description	1P
Fuse type	, CC
Control type	Toggle padlockable
Local signalling	Blown fuse indication
Utilisation category	AC-20B IEC 60947-3
[Ue] rated operational voltage	600 V AC
[Ie] rated operational current	30 A
[Ui] rated insulation voltage	600 V AC
[Uimp] rated impulse withstand voltage	6 kV
Short-circuit withstand	200 kA 600 V UL 512
Power dissipation in W	3 W maximum power dissipation by fuse

Complementary

Standards	UL 4248-1 UL 4248-4 CSA C22.2 No 4248-1 CSA C22.2 No 4248-4
Product certifications	UL Recognized[RETURN]CSA
Mounting Support	35 mm symmetrical DIN rail
Mounting position	Vertical +/- 23°
Connections - terminals	Screw clamp terminals 1 0.002...0.02 in ² (1...16 mm ²)rigid Screw clamp terminals 2 0.002...0.009 in ² (1...6 mm ²)rigid Screw clamp terminals 1 0.002...0.02 in ² (1...16 mm ²)flexible with or without Screw clamp terminals 2 0.002...0.009 in ² (1...6 mm ²)flexible with or without
Tightening torque	17.7 Lbf.In (2 N.m) PZ2 17.7 lbf.in (2 N.m) flat Ø 5.5 mm
Height	3.1 in (79.5 mm)
Width	0.7 in (17.5 mm)
Depth	2.4 in (61 mm)
Net Weight	0.093 lb(US) (0.042 kg)
Quantity per Set	Set of 12

Environment

Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Ambient air temperature for operation	-40...158 °F (-40...70 °C) with derating above 20°C
Operating altitude	0...6561.68 ft (0...2000 m) without derating
IP degree of protection	IP20
Pollution degree	3
Fire resistance	1760 °F (960 °C) IEC 60695-2-1
Compatibility code	DFCC

Ordering and shipping details

Category	US10CP121714
Discount Schedule	0CP1
GTIN	3389118321700
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.83 in (7.200 cm)
Package 1 Width	0.67 in (1.700 cm)
Package 1 Length	2.52 in (6.400 cm)
Package 1 Weight	1.552 oz (44.000 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	2.68 in (6.800 cm)
Package 2 Width	3.35 in (8.500 cm)
Package 2 Length	8.74 in (22.200 cm)
Package 2 Weight	20.106 oz (570.000 g)
Unit Type of Package 3	S03
Number of Units in Package 3	192
Package 3 Height	11.81 in (30.000 cm)
Package 3 Width	11.81 in (30.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	20.845 lb(US) (9.455 kg)

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
California proposition 65	WARNING: Cancer - www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	No

Contractual warranty

Warranty	18 months
----------	-----------